

SILVYN® FCL

SILVYN® FCL - conduit holder for SILVYN® FPAS



Halogen-free



Maximum vibration protection



Mechanical resistance



Assembly time



Robust



Reliability



Temperature-resistant

Benefits

Fast assembly
Easy to disassemble
High mechanical strength
Conduit retained by rib
No loose parts

Application range

In combination with protective conduit:
SILVYN® FPAS
Fastening of conduits on machine walls for all applications

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FCL

Product features

Removeable with a screwdriver
One-piece conduit holder

Product Make-up

One-piece conduit holder with borehole for fixation

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001171 ETIM 5.0 Class-Description: Holder for protective hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001171 ETIM 6.0 Class-Description: Holder for protective hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Temperature range:	-50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FCL

Article number	Nominal size	Hole Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FCL black				
55506905	10	5	10	10
55506915	13	5	13	10
55506925	16	5	16	10
55506985	18	6	18	10
55507405	20	6	20	10
55506935	21	6	21	10
55507415	25	6	25	10
55506945	28	6	28	10
55506955	34	6	34	10
55506965	42	6	42	10
55506975	54	6	54	10
SILVYN® FCL grey				
55506900	10	5	10	10
55506910	13	5	13	10
55506920	16	5	16	10
55506980	18	6	18	10
55507400	20	6	20	10
55506930	21	6	21	10
55507410	25	6	25	10
55506940	28	6	28	10
55506950	34	6	34	10
55506960	42	6	42	10
55506970	54	6	54	10