

## SILVYN® FLEXILOK 90° M

SILVYN® FLEXILOK 90° M - angled metric threaded conduit fitting

### Info

extremely economical  
90° elbow allows easy installation  
Small purchasing unit



Halogen-free



Assembly time



Space requirement



Temperature-resistant

### Benefits

Fast assembly  
Easy to assemble  
Cost-effective conduit gland  
No loose parts  
New space-saving design

### Application range

Mechanical engineering  
Control cabinet manufacturing  
Moving applications  
Applications with limited space  
Building Installation

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® FLEXILOK 90° M

### Product features

In black colour UV-resistant and weather-proofed  
One-piece slim design  
Halogen and cadmium-free

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

Metric connection thread  
90° elbow  
Special clamping system

### Note

Removeable with a screwdriver  
PG threaded versions are to be found in the online catalogue

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Norm references / Approvals:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-40°C to +120°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® FLEXILOK 90° M**

Article number	Metric size	Thread length mm	Suitable for SILVYN® FPAS	Suitable for conduit Ø (mm)	Pieces / PU
<b>SILVYN® FLEXILOK 90° M black</b>					
68100100	16 x 1.5	12	FPAS 16	15,8	10
68100105	20 x 1.5	13	FPAS 16	15,8	10
68100110	20 x 1.5	13	FPAS 21	21,2	10
68100115	25 x 1.5	15	FPAS 28	28,5	10
68100120	32 x 1.5	16	FPAS 34	34,5	10
<b>SILVYN® FLEXILOK 90° M grey</b>					
68100125	16 x 1.5	12	FPAS 16	15,8	10
68100130	20 x 1.5	13	FPAS 16	15,8	10
68100135	20 x 1.5	13	FPAS 21	21,2	10
68100140	25 x 1.5	15	FPAS 28	28,5	10
68100145	32 x 1.5	16	FPAS 34	34,5	10

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16