

SILVYN® FLEXILOK 90° PG

SILVYN® FLEXILOK 90° PG - angled PG threaded conduit fitting

Info

extremely economical
90° elbow allows easy installation
Small purchasing unit



Halogen-free



Assembly time



Space requirement



Temperature-resistant

Benefits

Fast assembly
Easy to assemble
Cost-effective conduit gland
No loose parts
New space-saving design

Application range

Mechanical engineering
Control cabinet manufacturing
Moving applications
Applications with limited space
Building Installation

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FLEXILOK 90° PG

Product features

In black colour UV-resistant and weather-proofed
One-piece slim design
Halogen and cadmium-free

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

PG connection thread
90° elbow
Special clamping system

Note

Removeable with a screwdriver

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Norm references / Approvals:

IEC EN 61386-23

Colour delivered:

Grey (RAL 7031)
Black (RAL 9005), UV-resistant

Material:

PA66
Halogen-free

Protection rating:

IP 66

Temperature range:

-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FLEXILOK 90° PG

Article number	Thread length mm	Suitable for SILVYN® FPAS	Suitable for conduit Ø (mm)	Pieces / PU
SILVYN® FLEXILOK 90° PG black				
68100150	10	FPAS 16	15,8	10
68100155	10	FPAS 16	15,8	10
68100160	10	FPAS 16	15,8	10
68100170	10	FPAS 21	21,2	10
68100165	11	FPAS 16	15,8	10
68100175	11	FPAS 21	21,2	10
68100180	12	FPAS 28	28,5	10
68100185	12	FPAS 34	34,5	10
SILVYN® FLEXILOK 90° PG grey				
68100190	10	FPAS 16	15,8	10
68100195	10	FPAS 16	15,8	10
68100200	10	FPAS 16	15,8	10
68100210	10	FPAS 21	21,2	10
68100205	11	FPAS 16	15,8	10
68100215	11	FPAS 21	21,2	10
68100220	12	FPAS 28	28,5	10
68100225	12	FPAS 34	34,5	10