

## SILVYN® FPAG-M

SILVYN® FPAG-M - conduit fitting for SILVYN® FPAS



Halogen-free



Maximum vibration protection



Assembly time



Optimum strain relief



Temperature-resistant



Variety of approval certifications

### Benefits

Fast assembly  
High-tensile  
Sealing  
Vibration protection

### Application range

In combination with protective conduit:  
SILVYN® FPAS  
Applications with strong vibrations

### Product features

In black colour UV-resistant and weather-proofed  
Removeable with a screwdriver

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® FPAG-M

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

Metric connection thread

Upper part with integrated all-round toothing

### Note

PG threaded versions are to be found in the online catalogue

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-50°C to +135°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® FPAG-M**

Article number	Metric size	For conduit with outer Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
<b>SILVYN® FPAG-M black</b>				
55506305	12 x 1.5	10	10	10
55506315	16 x 1.5	13	13	10
55506325	16 x 1.5	15.8	16	10
55506335	20 x 1.5	15.8	16	10
55507055	20 x 1.5	18.5	18	10
55506345	20 x 1.5	21.2	21	10
55506355	25 x 1.5	28.5	28	10
55506365	32 x 1.5	34.5	34	10
55506375	40 x 1.5	42.5	42	2
55506385	50 x 1.5	42.5	42	2
55506395	50 x 1.5	54.5	54	2
55506405	63 x 1.5	54.5	54	2
55506475	63 x 1.5	67.2	67	2
<b>SILVYN® FPAG-M grey</b>				
55506300	12 x 1.5	10	10	10
55506310	16 x 1.5	13	13	10
55506320	16 x 1.5	15.8	16	10
55506330	20 x 1.5	15.8	16	10
55507050	20 x 1.5	18.5	18	10
55506340	20 x 1.5	21.2	21	10
55506350	25 x 1.5	28.5	28	10
55506360	32 x 1.5	34.5	34	10
55506370	40 x 1.5	42.5	42	2
55506380	50 x 1.5	42.5	42	2
55506390	50 x 1.5	54.5	54	2
55506400	63 x 1.5	54.5	54	2
55506470	63 x 1.5	67.2	67	2

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16