

SILVYN® FPAX 90° M

SILVYN® FPAX 90° M - IP68/IP69 conduit fitting for SILVYN® FPAS

Info

IP66

IP67

IP68 (2 bar)

IP69



Maximum vibration protection



Mechanical resistance



Assembly time



Optimum strain relief



Robust



Temperature-resistant



UV-resistant



Waterproof



Variety of approval certifications

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FPAX 90° M

Benefits

90° elbow allows easy installation
Fast assembly
High tensile strength
Watertight
Vibration protection

Application range

In combination with protective conduit:
SILVYN® FPAS
Applications with strong vibrations

Product features

In black colour UV-resistant and weather-proofed
Removeable with a screwdriver

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

Metric connection thread
Body with inner sealing
Upper part with integrated all-round toothing
90° elbow

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP66 IP67 IP68 (2 bar) IP69
Temperature range:	-50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FPAX 90° M

Article number	Metric size	PL_PRODUKTBEZIEHUNG2	Pieces / PU
SILVYN® FPAX 90° M black			
55507300	16 x 1.5/1	FPAS 13	10
55507301	16 x 1.5/2	FPAS 16	10
55507302	20 x 1.5/1	FPAS 16	10
55507303	20 x 1.5/2	FPAS 21	10
55507304	25 x 1.5	FPAS 28	10
55507305	32 x 1.5	FPAS 34	10
55507306	40 x 1.5	FPAS 42	1
55507307	50 x 1.5/1	FPAS 42	1
55507308	50 x 1.5/2	FPAS 54	1
55507309	63 x 1.5	FPAS 54	1
SILVYN® FPAX 90° M grey			
55507310	16 x 1.5/1	FPAS 13	10
55507311	16 x 1.5/2	FPAS 16	10
55507312	20 x 1.5/1	FPAS 16	10
55507313	20 x 1.5/2	FPAS 21	10
55507314	25 x 1.5	FPAS 28	10
55507315	32 x 1.5	FPAS 34	10
55507316	40 x 1.5	FPAS 42	1
55507317	50 x 1.5/1	FPAS 42	1
55507318	50 x 1.5/2	FPAS 54	1
55507319	63 x 1.5	FPAS 54	1