

## SILVYN® FPAX-M

SILVYN® FPAX-M - IP68/IP69 conduit fitting for SILVYN® FPAS

### Info

IP66  
IP67  
IP68 (2bar)  
IP69



Maximum vibration protection



Assembly time



Optimum strain relief



Temperature-resistant



UV-resistant



Waterproof



Variety of approval certifications

### Benefits

Fast assembly  
High tensile strength  
Watertight  
Vibration protection

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® FPAX-M

### Application range

In combination with protective conduit:  
SILVYN® FPAS  
Applications with strong vibrations

### Product features

In black colour UV-resistant and weather-proofed  
Removeable with a screwdriver

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

Metric connection thread  
Body with inner sealing  
Upper part with integrated all-round toothing

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP66 IP67 IP68 (2bar) IP69
Temperature range:	-50 °C to +135 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® FPAX-M**

Article number	Metric size	Suitable for SILVYN® FPAS	Pieces / PU
<b>SILVYN® FPAX-M black</b>			
55506135	16 x 1.5/1	FPAS 13	10
55506145	16 x 1.5/2	FPAS 16	10
55506155	20 x 1.5/1	FPAS 16	10
55506165	20 x 1.5/2	FPAS 21	10
55506175	25 x 1.5	FPAS 28	10
55506185	32 x 1.5	FPAS 34	10
55506195	40 x 1.5	FPAS 42	2
55506205	50 x 1.5/1	FPAS 42	2
55506215	50 x 1.5/2	FPAS 54	2
55506225	63 x 1.5	FPAS 54	2
<b>SILVYN® FPAX-M grey</b>			
55506235	16 x 1.5/1	FPAS 13	10
55506245	16 x 1.5/2	FPAS 16	10
55506255	20 x 1.5/1	FPAS 16	10
55506265	20 x 1.5/2	FPAS 21	10
55506275	25 x 1.5	FPAS 28	10
55506285	32 x 1.5	FPAS 34	10
55506295	40 x 1.5	FPAS 42	2
55507265	50 x 1.5/1	FPAS 42	2
55507275	50 x 1.5/2	FPAS 54	2
55507285	63 x 1.5	FPAS 54	2

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16