

## SILVYN® FPAX P

SILVYN® FPAX P - plug for T/Y piece



### Benefits

Stop Plug for the SILVYN® FPAX T/Y system

### Application range

In combination with protective conduit:  
SILVYN® FPAS

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001172

ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001172

ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

PA66

Halogen-free

Polyester Elastomer

Protection rating:

IP66

IP67

IP68 (2 bar)

IP69

Temperature range:

-50°C to +135°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



## SILVYN® FPAX P

Article number	Nominal size	Suitable for SILVYN® FPAX T/Y	Pieces / PU
SILVYN® FPAX P			
55507370	16	16	5
55507371	21	21	5
55507372	28	28	5
55507373	34	34	3

Last Update (21.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16