

## SILVYN® FPAX T

SILVYN® FPAX T - divider in T-shape for SILVYN® FPAS



### Benefits

- Fast assembly
- High tensile strength
- Watertight
- Vibration protection

### Application range

In combination with protective conduit:  
SILVYN® FPAS

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001172 ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001172 ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free Polyester Elastomer
Protection rating:	IP66 IP67 IP68 (2 bar) IP69
Temperature range:	-50 °C to +135 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



## SILVYN® FPAX T

Article number	Nominal size	Hole Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAX T				
55507340	16	6	16	3
55507341	21	6	21	3
55507342	28	6	28	3
55507343	34	7	34	3
55507344	42	7	42	3

Last Update (30.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16