

SILVYN® FPAX Y

SILVYN® FPAX Y - divider in Y-shape for SILVYN® FPAS



Benefits

Fast assembly
High tensile strength
Watertight
Vibration protection

Application range

In combination with protective conduit:
SILVYN® FPAS

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001172

ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001172

ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

PA66
Halogen-free
Polyester Elastomer

Protection rating:

IP66
IP67
IP68 (2 bar)
IP69

Temperature range:

-50 °C to +135 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FPAX Y

Article number	Nominal size	Hole Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAX Y				
55507350	16-13-13	4	1x16 / 2x13	3
55507351	21-16-16	5	1x21 / 2x16	3
55507352	28-21-21	6	1x28 / 2x21	3
55507353	34-28-28	6.5	1x34 / 2x28	3