

## SILVYN® FPAX Y

SILVYN® FPAX Y - divider in Y-shape for SILVYN® FPAS



### Benefits

- Fast assembly
- High tensile strength
- Watertight
- Vibration protection

### Application range

In combination with protective conduit:  
SILVYN® FPAS

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001172 ETIM 5.0 Class-Description: Coupler for corrugated plastic hoses
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001172 ETIM 6.0 Class-Description: Coupler for corrugated plastic hoses
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free Polyester Elastomer
Protection rating:	IP66 IP67 IP68 (2 bar) IP69
Temperature range:	-50 °C to +135 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® FPAX Y**

Article number	Nominal size	Hole Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAX Y				
55507350	16-13-13	4	1x16 / 2x13	3
55507351	21-16-16	5	1x21 / 2x16	3
55507352	28-21-21	6	1x28 / 2x21	3
55507353	34-28-28	6.5	1x34 / 2x28	3

Last Update (22.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16