

SILVYN® AFW-PA

SILVYN® AFW-PA is a one-piece angled connection flange especially designed for SILVYN® MAXI PA



Assembly time



Robust



Reliability

Benefits

Tear-resistant connection
Secure conduit insertion

Application range

In combination with protective conduit
SILVYN® MAXI PA
Mechanical engineering
Bundling and guiding of cables and wires

Product Make-up

One-piece 90° elbow connector with clap mechanism specifically designed for use with the SILVYN® MAXI PA. Thanks to the special design, the conduit can be pre-locked and mounted ready for connection

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Colour delivered:

Grey (RAL 7001)

Last Update (05.03.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® AFW-PA

	Black (RAL 9005), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 54 IP 65 with AFG-PA/AFW-PA seal
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® AFW-PA

Article number	Nominal size	Pieces / PU
SILVYN® AFW-PA 90° grey		
55001090	70	1
55001091	95	1
SILVYN® AFW-PA 90° black		
55001093	70	1
55001092	95	1