

## SILVYN® gasket AFG-PA / AFW-PA

SILVYN® gasket AFG-PA / AFW-PA is a sealing ring for usage with the connection flange for large diameters



Assembly time



Robust



Reliability

### Benefits

Increases the IP degree of protection of SILVYN® AFG-PA and SILVYN® AFW-PA

### Application range

In combination with protective conduit  
 SILVYN® MAXI PA  
 Mechanical engineering  
 Bundling and guiding of cables and wires

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000781 ETIM 5.0 Class-Description: Sealing for hose screw connection
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000781 ETIM 6.0 Class-Description: Sealing for hose screw connection
Colour delivered:	Grey (RAL 7001) Black (RAL 9005), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 54 IP 65 with AFG-PA/AFW-PA seal
Temperature range:	-40 °C to +115 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® gasket AFG-PA / AFW-PA

Prices are net prices without VAT and surcharges. Sale to business customers only.



## SILVYN® gasket AFG-PA / AFW-PA

Article number	Nominal size	Pieces / PU
SILVYN® seal for AFG-PA, AFW-PA		
55001082	70	1
55001083	95	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16