

## SILVYN® HG-M

SILVYN® HG-M - conduit fitting for SILVYN® HCC



UV-resistant

### Benefits

Easy to disassemble  
High-tensile  
Sealing

### Application range

In combination with protective conduit  
SILVYN® HCC

### Product Make-up

Metric connection thread  
Body with sealing and clamping ring  
Cap nut

### Note

UV-resistant and weather-resistant

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

PA6

Protection rating:

IP 65

Temperature range:

-25°C to +100°C

Last Update (03.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® HG-M

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



## SILVYN® HG-M

Article number	Article designation	Overall length mm	Thread length mm	Suitable for SILVYN® HCC	Pieces / PU
55501650	40 x 1,5	53	15	40	20
55501660	50 x 1,5	57.4	15	50	16
55501670	63 x 1,5	74	20	63	8

Last Update (03.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16