

SILVYN® SPLIT COS

SILVYN® SPLIT COS is a one-piece conduit holder to fix a cable protection conduit



Halogen-free



Assembly time



Temperature-resistant



UV-resistant

Benefits

- Fast assembly
- Easy to disassemble
- High tensile strength
- Conduit retained by rib
- No loose parts

Application range

In combination with protective conduit:
SILVYN® SPLIT
Fastening of conduits on machine walls for all applications

Product features

One-piece conduit holder

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001171

ETIM 5.0 Class-Description: Holder for protective hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001171

ETIM 6.0 Class-Description: Holder for protective hose

Last Update (12.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® SPLIT COS

Colour delivered:	Black (RAL 9005), UV-resistant
Material:	Halogen-free PA
Temperature range:	-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® SPLIT COS

Article number	Nominal size	Hole Ø (mm)	Suitable for SILVYN® SPLIT	Pieces / PU
61806693	6	M3	6	100
61806690	10	M3	10	100
61806676	10	M5	10	100
61806694	11	M3	11	100
61806700	14	M3	14	100
61806677	14	M5	14	50
61806695	16	M5	16	50
61806696	16	M6	16	50
61806710	20	M5	20	50
61806678	20	M6	20	50
61806720	23	M5	23	50
61806679	23	M6	23	50
61806697	29	M5	29	50
61806698	29	M6	29	50
61806730	37	M6	37	20
61806740	45	M6	45	20
61806699	70	M6	70	10

Last Update (12.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16