

SILVYN® KCLICK 90° M

SILVYN® KCLICK-M - metrische conduit fitting for SILVYN® RILL



Assembly time



Temperature-resistant



Variety of approval certifications

Benefits

- 90° elbow allows easy installation
- Fast assembly
- Easy to disassemble
- High-tensile
- High sealing performance

Application range

- In combination with protective conduit:
- SILVYN® RILL PA 6
- SILVYN® RILL PA 12
- For applications with limited space
- Rotating applications

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

- Metric connection thread
- 90° elbow
- Body with inner sealing
- Upper part with snap-in sleeve

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KCLICK 90° M

Note

PG threaded versions are to be found in the online catalogue

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® KLICK 90° M

Article number	Metric size	Thread length mm	Clear opening (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK 90° M grey						
55501110	10 x 1.0	12	6	10	10	50
55501120	12 x 1.5	12	8	13	13	50
55501130	16 x 1.5/1	12	12	13	13	50
55501140	16 x 1.5/2	12	12	15.8	16	50
55501150	20 x 1.5/1	13	15	15.8	16	50
55501160	20 x 1.5/2	13	15	21.2	21	50
55501170	25 x 1.5/1	13	18	21.2	21	50
55501180	25 x 1.5/2	13	18	28.5	28	25
55501190	32 x 1.5/1	15	24	28.5	28	25
55501200	32 x 1.5/2	15	24	34.5	34	10
55501210	40 x 1.5/1	15	32	34.5	34	10
55501220	40 x 1.5/2	15	32	42.5	42	10
55501230	50 x 1.5/1	16	39	42.5	42	10
55501240	50 x 1.5/2	16	39	54.5	54	5
55501250	63 x 1.5	16	53	54.5	54	5
SILVYN® KLICK 90° M black						
55501115	10 x 1.0	12	6	10	10	50
55501125	12 x 1.5	12	8	13	13	50
55501135	16 x 1.5/1	12	12	13	13	50
55501145	16 x 1.5/2	12	12	15.8	16	50
55501155	20 x 1.5/1	13	15	15.8	16	50
55501165	20 x 1.5/2	13	15	21.2	21	50
55501175	25 x 1.5/1	13	18	21.2	21	50
55501185	25 x 1.5/2	13	18	28.5	28	25
55501195	32 x 1.5/1	15	24	28.5	28	25
55501205	32 x 1.5/2	15	24	34.5	34	10
55501215	40 x 1.5/1	15	32	34.5	34	10
55501225	40 x 1.5/2	15	32	42.5	42	10
55501235	50 x 1.5/1	16	39	42.5	42	10
55501245	50 x 1.5/2	16	39	54.5	54	5
55501255	63 x 1.5	16	53	54.5	54	5