

## SILVYN® KLICK GPZ-M

SILVYN® KLICK GPZ-M - metric conduit fitting with integrated cable strain relief for SILVYN® RILL



Wide clamping range



Assembly time



Optimum strain relief



Temperature-resistant



Variety of approval certifications

### Benefits

- Fast assembly
- Easy to disassemble
- Additional cable strain relief
- Additional cable sealing

### Application range

In combination with protective conduit:

- SILVYN® RILL PA 6
- SILVYN® RILL PA 12
- Robot-building

Used in areas where cables and wires need to be provided with strain relief and additional sealing

### Norm references / Approvals

UL FILENUMBER E308201

Last Update (27.05.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® KLICK GPZ-M

### Product Make-up

Metric connection thread  
Cable gland  
Body with inner sealing  
Upper part with snap-in sleeve

### Note

PG threaded versions are to be found in the online catalogue

### Technical Data

|                        |   |
|------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001176<br>ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001176<br>ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose |
| Colour delivered:      | Grey (RAL 7031)<br>Black (RAL 9011), UV-resistant   |
| Material:              | PA6   |
| Protection rating:     | IP 68<br>IP 69  |
| Temperature range:     | -40 °C to +115 °C   |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® KLICK GPZ-M**

| Article number             | Metric size | Clamping range in mm | SW wrench size mm | Thread length mm | Clear opening (mm) | For conduit with outer Ø (mm) | Suitable for SILVYN® RILL | Pieces / PU |
|----------------------------|-------------|----------------------|-------------------|------------------|--------------------|-------------------------------|---------------------------|-------------|
| SILVYN® KLICK, GPZ-M grey  |             |                      |                   |                  |                    |                               |                           |             |
| 55500800                   | 12 x 1.5    | 4 - 6.5              | 16                | 8                | 6.5                | 10                            | 10                        | 20          |
| 55500810                   | 16 x 1.5    | 5 - 9.5              | 18                | 8                | 9.5                | 13                            | 13                        | 20          |
| 55500820                   | 20 x 1.5    | 8 - 12               | 24                | 8                | 13                 | 15.8                          | 16                        | 20          |
| 55500830                   | 25 x 1.5    | 11 - 16              | 27                | 8                | 16                 | 21.2                          | 21                        | 10          |
| 55500840                   | 32 x 1.5    | 15 - 21              | 34                | 10               | 18                 | 28.5                          | 28                        | 10          |
| 55500850                   | 40 x 1.5    | 16 - 26              | 40                | 10               | 25                 | 34.5                          | 34                        | 10          |
| 55500860                   | 50 x 1.5    | 27 - 35              | 55                | 12               | 32                 | 42.5                          | 42                        | 10          |
| 55500870                   | 63 x 1.5    | 32 - 42              | 65                | 12               | 44                 | 54.5                          | 54                        | 10          |
| SILVYN® KLICK, GPZ-M black |             |                      |                   |                  |                    |                               |                           |             |
| 55500805                   | 12 x 1.5    | 4 - 6.5              | 16                | 8                | 6.5                | 10                            | 10                        | 20          |
| 55500815                   | 16 x 1.5    | 5 - 9.5              | 18                | 8                | 9.5                | 13                            | 13                        | 20          |
| 55500825                   | 20 x 1.5    | 8 - 12               | 24                | 8                | 13                 | 15.8                          | 16                        | 20          |
| 55500835                   | 25 x 1.5    | 11 - 16              | 27                | 8                | 16                 | 21.2                          | 21                        | 10          |
| 55500845                   | 32 x 1.5    | 15 - 21              | 34                | 10               | 18                 | 28.5                          | 28                        | 10          |
| 55500855                   | 40 x 1.5    | 16 - 26              | 40                | 10               | 25                 | 34.5                          | 34                        | 10          |
| 55500865                   | 50 x 1.5    | 27 - 35              | 55                | 12               | 32                 | 42.5                          | 42                        | 10          |
| 55500875                   | 63 x 1.5    | 32 - 42              | 65                | 12               | 44                 | 54.5                          | 54                        | 10          |

Last Update (27.05.2023)

©2023 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16