

SILVYN® MPC 45° M

SILVYN® MPC 45° M - conduit fitting for use with SILVYN® EL/ELU/ELO/ELT



Halogen-free



Mechanical resistance



Assembly time



Oil-resistant



Optimum strain relief



Robust



Temperature-resistant



UV-resistant

Benefits

All-purpose

Fast and easy assembly

45° elbow enables best assembling

Application range

In combination with protective conduit

SILVYN® EL/ELU/ELO/ELT/ELR (helically formed and smooth conduits)

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® MPC 45° M

Product features

Dust protection
Moisture-protection
Ensures high tensile strength and mechanical protection

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

Metric connection thread
45° elbow with integrated conduit connection

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Black (RAL 9005), UV-resistant Grey, RAL 7001
Material:	PA66 Halogen-free
Protection rating:	IP 65 with helically formed conduits IP 67 + IP 68 (2bar) with smooth conduits
Temperature range:	-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® MPC 45° M

Article number	Metric size	Clear opening (mm)	Suitable for SILVYN® EL/ELU/ELO/ELT/ELR	Pieces / PU
SILVYN® MPC 45° M black				
55502431	20 x 1.5/1	10.5	16	10
55502432	20 x 1.5/2	14.5	20	10
55502433	25 x 1.5	19	25	10
55502434	32 x 1.5	24.5	32	10
SILVYN® MPC 45° M grey				
55502435	20 x 1.5/1	10.5	16	10
55502436	20 x 1.5/2	14.5	20	10
55502437	25 x 1.5	19	25	10
55502438	32 x 1.5	24.5	32	10