

SILVYN® MPC

SILVYN® MPC - conduit fitting for use with SILVYN® EL/ELU/ELO/ELT



Halogen-free



Mechanical resistance



Assembly time



Oil-resistant



Optimum strain relief



Robust



Temperature-resistant



UV-resistant

Benefits

All-purpose

Fast and easy assembly

Application range

In combination with protective conduit:

SILVYN® EL/ELU/ELO/ELT/ELR (helically formed and smooth conduits)

SILVYN® MPC

Product features

Dust protection
Moisture-protection
Ensures high tensile strength and mechanical protection

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

PG connection thread
Hexagonal collar with integrated conduit connection

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Black (RAL 9005), UV-resistant Grey, RAL 7001
Material:	PA66 Halogen-free
Protection rating:	IP 65 with helically formed conduits IP 67 + IP 68 (2bar) with smooth conduits
Temperature range:	-40 °C to +120 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® MPC

Article number	PG size	Clear opening (mm)	Suitable for SILVYN® SI	Suitable for SILVYN® SP/SP-PU	Suitable for SILVYN® EL/ELU/ELO/ELT/ELR	Pieces / PU
SILVYN® MPC black						
55502470	9	9	11 x 14	-	12	10
55502471	11	10.5	13 x 16	12 x 16	16	10
55502472	13.5	10.5	13 x 16	12 x 16	16	10
55502494	13.5	14.5	-	16 x 20	20	10
55502473	16	14.5	-	16 x 20	20	10
55502474	21	19	-	22 x 27	25	10
55502476	29	24.5	-	-	30	10
55502495	29	24.5	-	-	32	10
55502477	36	33	-	-	40	2
55502478	42	39	-	-	50	2
55502479	48	48	-	-	63	1
SILVYN® MPC grey						
55502496	9	9	11 x 14	-	12	10
55502497	11	10.5	13 x 16	12 x 16	16	10
55502498	13.5	10.5	13 x 16	12 x 16	16	10
55502499	13.5	14.5	-	16 x 20	20	10
55502451	16	14.5	-	16 x 20	20	10
55502452	21	19	-	22 x 27	25	10
55502453	29	24.5	-	-	30	10
55502454	29	24.5	-	-	32	10
55502455	36	33	-	-	40	2
55502456	42	39	-	-	50	2
55502457	48	48	-	-	63	1

Last Update (06.06.2023)

©2023 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16