

SILVYN® LKI-M

SILVYN® LKI-M - swivelling plastic conduit fitting

Info

Swivelling upper part with integrated inner sleeve



Maximum vibration protection



Assembly time



Space requirement

Benefits

Fast and easy assembly

Vibration protection

High-tensile

Can be rotated

Application range

In combination with protective conduit:

SILVYN® FPS

SILVYN® FD-PU

Robot-building

For rotating applications

Product features

Smooth inner surface

Slim construction

Product Make-up

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LKI-M

Metric connection thread
Swivelling upper part with integrated inner sleeve

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Colour delivered:	Silver grey (RAL 7001)
Material:	PP
Protection rating:	IP 54
Temperature range:	-10°C to +110°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LKI-M

Article number	Metric size	SW wrench size mm	Overall length mm	Thread length mm	Clear opening (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® LKI-M							
55501400	12 x 1.5	16	38	10	5.5	7 x 10	50
55501410	16 x 1.5	19	39.5	10	9.5	10 x 14	50
55501420	20 x 1.5	22	42	10	11.5	13 x 17	50
55501430	25 x 1.5	27	48	11	14.5	16 x 21	50
55501440	32 x 1.5	35	58	12	19.5	22 x 27	25
55501450	40 x 1.5	45	59	12	27	29 x 36	25
55501460	50 x 1.5	54	62.5	12	35.5	38 x 45	25
55501470	63 x 1.5	65	68	15	46	48 x 56	10

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16