

SILVYN® LKI

SILVYN® LKI - swivelling plastic conduit fitting

Info

Swivelling upper part with integrated inner sleeve



Maximum vibration protection



Assembly time



Space requirement

Benefits

Fast and easy assembly

Vibration protection

High-tensile

Can be rotated

Application range

In combination with protective conduit:

SILVYN® FPS

SILVYN® FD-PU

Robot-building

For rotating applications

Product features

Smooth inner surface

Slim construction

Product Make-up

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LKI

PG connection thread
Swivelling upper part with integrated inner sleeve

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Colour delivered:	Silver grey (RAL 7001)
Material:	PP
Protection rating:	IP 54
Temperature range:	-10°C to +110°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LKI

Article number	PG size	SW wrench size mm	Overall length mm	Thread length mm	Clear opening (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® LKI							
55000000	7	16	38	10	5.5	7 x 10	50
55000010	9	19	39.5	10	9.5	10 x 14	50
55000020	11	22	42	10	11.5	13 x 17	50
55000030	13.5	24	42	10	13	15 x 19	50
55000040	16	27	48	11	14.5	16 x 21	50
55000050	21	35	58	11	19.5	22 x 27	25
55000060	29	45	59	12	27	29 x 36	25
55000070	36	54	62.5	12	35.5	38 x 45	25
55000090	48	65	68	15	46	48 x 56	10

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16