

SILVYN® MSK-M EE

SILVYN® MSK-M EE - nickel-plated brass conduit fitting with integrated cable strain relief

Info

Integrated SKINTOP® cable strain relief



Wide clamping range



Maximum vibration protection



Assembly time



Optimum strain relief



Robust



Integrated SKINTOP® cable gland

Benefits

Optimum cable and conduit strain relief
Maximum cable sealing
Fast and easy assembly
Wide clamping range
Anti-turn protection

Application range

In combination with protective conduit:
SILVYN® FPS
SILVYN® FD-PU

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® MSK-M EE

For indoor and outdoor use

Used in areas where cables and wires need to be provided with strain relief and additional sealing

Product features

Combination of SILVYN® and SKINTOP®

Product Make-up

SKINTOP® MS-M cable gland or

SKINTOP® MS-SC-M EMC connection

SILVYN® conduit connection via inner sleeve and cap nut

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Material:

Basis type:

Body: nickel-plated brass

Conduit connector seal: CR/NBR

Tube seal: TPE

Protection rating:

Cable: IP 68

Conduit:

IP 54 with SILVYN® FPS, FD-PU

Temperature range:

-30 °C to +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® MSK-M EE

Article number	Metric size	Clamping range in mm	Clear opening (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® MSK-M for SILVYN® FPS/FD-PU					
55506070	12 x 1.5	3.0 - 7.0	6	7 x 10	5
55506071	16 x 1.5	4.5 - 10.0	9.3	10 x 14	5
55506072	20 x 1.5	7.0 - 13.0	11.5	13 x 17	5
55506073	25 x 1.5	9.0 - 17.0	13.4	16 x 21	5
55506074	32 x 1.5	11.0 - 21.0	19.5	22 x 27	5
55506075	40 x 1.5	19.0 - 28.0	27	29 x 36	1
55506076	50 x 1.5	27.0 - 35.0	36.4	38 x 45	1
55506077	63 x 1.5	34.0 - 45.0	46	48 x 56	1
SILVYN® MSK-SC-M for SILVYN® FPS/FD-PU					
55506101	16 x 1.5	4.5 - 10.0	9.3	10 x 14	5
55506102	20 x 1.5	7.0 - 13.0	11.5	13 x 17	5
55506103	25 x 1.5	9.0 - 17.0	13.4	16 x 21	5
55506104	32 x 1.5	11.0 - 21.0	19.5	22 x 27	5
55506105	40 x 1.5	19.0 - 28.0	27	29 x 36	1
55506106	50 x 1.5	27.0 - 35.0	36.4	38 x 45	1

SILVYN® MSK-M EE

