

SILVYN® US EE

SILVYN® US is a PG threaded nickel-plated brass conduit fitting that offers IP40 / IP54 / IP66 protection degree depending on the used conduit



Maximum vibration protection



Space requirement



Robust



Temperature-resistant

Benefits

High tensile strength
Space-saving
Vibration protection
All-purpose
Fast and easy assembly

Application range

In combination with protective conduit:
SILVYN® FPS
SILVYN® FD-PU
Mechanical engineering
Plant engineering

Product features

Compact design

Product Make-up

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® US EE

PG connection thread
Hexagonal collar
Threaded sleeve
Sealing element
Cap nut

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Material:

Body: nickel-plated brass

Sealing ring: TPE

Protection rating:

IP 54 (with SILVYN® FPS, FD-PU)

Temperature range:

-40°C to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® US EE

Article number	PG size	Clear opening (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® US for SILVYN® FPS / FD-PU				
55502651	7	6	10	50
55502652	9	9	14	50
55502653	11	11.5	17	50
55502654	13.5	13	19	50
55502655	16	14.5	21	50
55502656	21	19.5	27	25
55502657	29	26.5	36	25
55502658	36	36	45	20
55502659	48	45.5	56	10

SILVYN® US EE

