


SILVYN® USK

SILVYN® USK - PG threaded conduit fitting



Maximum vibration protection



Assembly time

Benefits

Fast and easy assembly
Vibration protection
No extra parts necessary

Application range

In combination with protective conduit:
SILVYN® FPS/ FD-PU
SILVYN® SP/SP-PU
Indoor applications
Light mechanical stress

Product features

Large wrench sizes

Product Make-up

PG connection thread
Hexagonal collar
Threaded sleeve
Cap nut

Note

Included: SILVYN® EE-K inner sleeve

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® USK

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001178 ETIM 5.0 Class-Description: Screw connection for protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001178 ETIM 6.0 Class-Description: Screw connection for protective plastic hose
Colour delivered:	Silver grey (RAL 7001)
Material:	PP
Protection rating:	IP 54
Temperature range:	-10°C to +110°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® USK

Article number	PG size	SW 1/2 mm	Overall length mm	Thread length mm	Clear opening (mm)	Suitable for SILVYN® FD-PU/FPS	Suitable for SILVYN® SP/SP-PU	Pieces / PU
SILVYN® USK								
52005810	7	16.0 / 18.0	40	10	6	7 x 10	-	50
52005820	9	21.0 / 23.0	41	10	9	10 x 14	10 x 14	50
52005830	11	24.0 / 27.0	41	10	11	13 x 17	12 x 16	50
52005840	13.5	26.0 / 29.0	41	10	13	15 x 19	14 x 18	50
52005850	16	29.0 / 32.0	42	11	14.5	16 x 21	16 x 20	50
52005860	21	36.0 / 40.0	48	11	19.5	22 x 27	22 x 27	25
52005870	29	45.0 / 49.0	48	12	27	29 x 36	30 x 36	25
52005880	36	53.0 / 58.0	48	12	36	38 x 45	38 x 44	25
52005900	48	65.0 / 70.0	57	15	46	48 x 56	49 x 56	10