

SILVYN® HIPROJACKET AMG

SILVYN® HIPROJACKET AMG - nickel-plated brass conduit fitting for SILVYN® HIPROJACKET

Info

Suitable fitting for use with SILVYN® HIPROJACKET



Mechanical resistance



Robust



Temperature-resistant

Benefits

High tensile strength

For high mechanical stress

45° and 90° elbow enables optimal assembly

Application range

In combination with protective conduit:

SILVYN® HIPROJACKET

Product Make-up

Connection thread metric/PG

Hexagonal collar, straight/45° elbow/90° elbow

Threaded sleeve

Cap nut

Note

It is possible to extend the temperature range by removing the plastic components

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® HIPROJACKET AMG

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
On request:	NPT connection thread
Material:	Body: nickel-plated brass Clamping ring: nickel-plated brass O-ring: NBR
Protection rating:	IP 54 IP 67 if SILVYN® HIPROSILTAPE is also used
Temperature range:	-45°C to +105°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® HIPROJACKET AMG

Article number	Metric size	PG size	Pieces / PU
SILVYN® HIPROJACKET AMG M			
55503516	16 x 1.5	-	50
55503517	20 x 1.5	-	50
55503518	25 x 1.5	-	25
55503519	32 x 1.5	-	10
55503520	40 x 1.5	-	5
55503521	50 x 1.5	-	5
55503522	63 x 1.5	-	4
SILVYN® HIPROJACKET AMG 45° M			
55503523	16 x 1.5	-	50
55503524	20 x 1.5	-	50
55503525	25 x 1.5	-	25
55503526	32 x 1.5	-	10
55503527	40 x 1.5	-	5
55503528	50 x 1.5	-	5
55503529	63 x 1.5	-	4
SILVYN® HIPROJACKET AMG 90° M			
55503530	16 x 1.5	-	50
55503531	20 x 1.5	-	50
55503532	25 x 1.5	-	25
55503533	32 x 1.5	-	10
55503534	40 x 1.5	-	5
55503535	50 x 1.5	-	5
55503536	63 x 1.5	-	4
SILVYN® HIPROJACKET AMG PG			
55503537	-	9	50
55503538	-	11	50
55503539	-	13.5	50
55503540	-	16	50
55503541	-	21	25
55503542	-	29	10
55503543	-	36	5
55503544	-	42	5
55503499	-	48	4
SILVYN® HIPROJACKET AMG 45° PG			

SILVYN® HIPROJACKET AMG

Article number	Metric size	PG size	Pieces / PU
55503500	-	11	50
55503501	-	13.5	50
55503502	-	16	50
55503503	-	21	25
55503504	-	29	10
55503505	-	36	5
55503506	-	42	5
55503507	-	48	4
SILVYN® HIPROJACKET AMG 90° PG			
55503508	-	11	50
55503509	-	13.5	50
55503510	-	16	50
55503511	-	21	25
55503512	-	29	10
55503513	-	36	5
55503514	-	42	5
55503515	-	48	4

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16