


## Tie socket self-adhesive

Screw/adhesive socket for fastening cable ties



Flame-retardant



Halogen-free

### Benefits

Option for cross-mounting / double-mounting on the crossover points of the cable harness  
Easy to handle

### Application range

The cable ties are slotted through the eyelets for fixing cables or other items to the wall  
Wiring of switch cabinets, motor vehicles and office machines, etc.

### Norm references / Approvals

Self-extinguishing in accordance with  
UL 94 V-2 (without adhesive tape)

### Note

Walls must be smooth and grease-free  
Minimum adhesive application time: 10 sec, recommended adhesive curing time: 24 h

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000449

ETIM 5.0 Class-Description: Mounting base and -element for cable ties

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000449

ETIM 6.0 Class-Description: Mounting base and -element for cable ties

Colour delivered:

Black  
Natural colour

Material:

Polyamide 6.6  
Halogen-free and silicone-free

Temperature range:

-15 °C to +50 °C

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## Tie socket self-adhesive

Minimum working temperature: +10°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## Tie socket self-adhesive

Article number	Article description	Colour	Diameter (mm)	Tie width (mm)	Length x width (mm)	Pieces / PU
61718612	Adhesive socket 19 x 19 NA	natural	3.2	3.6	19.0 x 19.0	100
61718611	Adhesive socket 19 x 19 BK	black	3.2	3.6	19.0 x 19.0	100
61718614	Adhesive socket 28 x 28 NA	natural	5,3	5.3	28.0 x 28.0	100
61718613	Adhesive socket 28 x 28 BK	black	5,3	5.3	28.0 x 28.0	100