

DKK double clamp

DKK double clamp for fastening cables and conductors



Benefits

Secure protection without restricting the mobility of the cable cores
Wide clamping range

Application range

Simple and reliable mounting clamps for lift control cables

Note

Installation guidelines for ÖLFLEX® -LIFT RH and RS lift control cables can be found in the appendix T5
Maximum load for each clamp: 800 N (80 kg)
Only for vertical assembly

Included

Impact anchor, screws and safety discs are supplied as installation accessories

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000127

ETIM 5.0 Class-Description: Fixing clip

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000127

ETIM 6.0 Class-Description: Saddle

Temperature range:

High mechanical load: +65 °C

Low mechanical load: +100 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

DKK double clamp

Article number	Article designation	For cable Ø (mm)	Length x width x height (mm)	Weight (kg/piece)	Pieces / PU
DKK					
52026010	DKK 18	15 - 18	125.0 x 85.0 x 120.0	2	1
52026012	DKK 26	19 - 26	125.0 x 85.0 x 120.0	2	1