

## EKK single clamp

EKK single clamp for fastening cables and conductors



### Benefits

Secure protection without restricting the mobility of the cable cores  
Wide clamping range

### Application range

Simple and reliable mounting clamps for lift control cables

### Note

Installation guidelines for ÖLFLEX® -LIFT RH and RS lift control cables can be found in the appendix T5  
Maximum load for each clamp: 800 N (80 kg)  
Only for vertical assembly

### Included

Impact anchor, screws and safety discs are supplied as installation accessories

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000127 ETIM 5.0 Class-Description: Fixing clip
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000127 ETIM 6.0 Class-Description: Saddle
Temperature range:	High mechanical load: +65 °C Low mechanical load: +100 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## EKK single clamp

Article number	Article designation	For cable Ø (mm)	Length x width x height (mm)	Weight (kg/piece)	Pieces / PU
Single clamp					
52026000	EKK 18	15 - 18	125.0 x 45.0 x 120.0	1.4	1
52026011	EKK 26	19 - 26	125.0 x 45.0 x 120.0	1.4	1

Last Update (26.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16