

DIN assorted boxes conductor end sleeves

The DIN conductor end sleeves are stored in a practical box with an assortment of cross-sections, making them readily available.



Halogen-free

Benefits

Convenient assortment boxes - several diameters always at your fingertips

Norm references / Approvals

The insulated conductor end sleeves are in accordance with DIN 46228, part 4 (0.25 mm² and 0.34 mm² not standardised) in assortment boxes

Product Make-up

DIN assortment box I:

30 x 0.25 - 6 mm BU, 30 x 0.34 - 6 mm YE, 30 x 0.5 - 8 mm WH, 30 x 0.75 - 8 mm GY, 30 x 1.00 - 8 mm RD

DIN assortment box II:

50 x 0.5 - 8 mm WH, 100 x 0.75 - 8 mm GY, 100 x 1.00 - 8 mm RD, 100 x 1.5 - 8 mm BK, 50 x 2.5 - 8 mm BU

DIN assortment box III:

40 x 4.00 - 10 mm GY, 20 x 6.0 - 12 mm YE, 20 x 10.00 - 12 mm RD, 10 x 16.00 - 12 mm BU

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000524

ETIM 5.0 Class-Description: Assortment box for installation- and connection material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000524

ETIM 6.0 Class-Description: Assortment box for installation- and connection material

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

DIN assorted boxes conductor end sleeves

Article number	Article designation	For mm ²	Suitable crimp insert	Contents (unit)	PU
DIN assortment box					
61802040	DIN assortment box I	0.25 - 1	PEW 12.090	150 x 1	1
61802041	DIN assortment box II	0.5 - 2.5	PEW 12.090	400 x 1	1
61802042	DIN assortment box III	4 - 16	PEW 12.090 / PEW 12.091	100 x 1	1