

T 2288 pressing pliers

T 228: Pressing Pliers for cable lugs and butt connectors, 10-25 mm², crimping profile: hexagonal, tested according to SEN 245010



Benefits

Forced locking guarantees complete pressing
Handy for on-site electric fitters
Small size

Application range

For pressing copper connections of 10 - 25 mm²
For pressing tube cable lugs (KRT) and butt connectors

Norm references / Approvals

Tested in accordance with standard SS-EN61238-1

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000168

ETIM 5.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000168

ETIM 6.0 Class-Description: Crimp tool cable lugs, cable end sleeves, screen connection

Note:

Crimping profile: Hexagonal

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

T 2288 pressing pliers

Article number	Article designation	For mm²	Crimping profile	Weight (kg)	Length (mm)	Pieces / PU
61790961	T 2288	10 - 25	hexagon	0.6	300	1