

## KNIPEX Cable shear

KNIPEX cable shears for conductors with an outer diameter of up to 20 mm, ergonomic design means it is particularly easy to use, manufactured in Germany

### Info

Less power required due to favourable transmission ratio and new blade geometry



### Benefits

Special two-blade structure divides the cutting process into pre-cut and post-cut

Easy and clean cut by using only one hand

High ergonomics thanks to multi-component handles

Insulated handles allow working under voltage up to 1000V

### Application range

Cuts copper and aluminium cables

### Product features

Precision ground, hardened blades

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000142

ETIM 5.0 Class-Description: Cable shears

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000142

ETIM 6.0 Class-Description: Cable shears

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC

VDE-tested

Material:

High-grade special tool steel, forged, chrome plated

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**KNIPLEX Cable shear**

Article number	Article designation	Cable diameter mm	Weight (kg)	Length (mm)
62120523	Cable shear KASI 20	20	0.34	200

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16