

KNIPEX Diagonal cutter

KNIPEX X-Cut® Diagonal cutter with insulated handle for precise cutting

Info

Narrow head style for use in confined areas



Benefits

High ergonomics thanks to multi-component handles
Insulated handles allow working under voltage up to 1000V

Application range

For soft and hard wire

Product features

Precision ground, hardened blades

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000142

ETIM 5.0 Class-Description: Cable shears

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000142

ETIM 6.0 Class-Description: Cable shears

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC

VDE-tested

Material:

Vanadium steel, forged, multi stage oil-hardened

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

KNIPEX Diagonal cutter

Article number	Article designation	Soft wire mm	Medium hard wire mm	Hard wire mm	Weight (kg)	Length (mm)
KNIPEX Diagonal cutter						
62120520	Diagonal cutter SESI 16	4	3	2	0.216	160

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16