

KNIPEX High leverage diagonal cutter

KNIPEX High leverage diagonal cutter with insulated handle for precise cutting

Info

High cutting performance with minimum effort



Benefits

High ergonomics thanks to multi-component handles
Insulated handles allow working under voltage up to 1000V

Application range

For all sorts of wire including piano wire

Product features

Precision ground, hardened blades

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000142

ETIM 5.0 Class-Description: Cable shears

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000142

ETIM 6.0 Class-Description: Cable shears

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC /
1500V DC

VDE-tested

Material:

Vanadium steel, forged, multi stage oil-hardened

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

KNIPEX High leverage diagonal cutter

Article number	Article designation	Medium hard wire mm	Hard wire mm	Pianowire mm	Weight (kg)	Length (mm)
KNIPEX High leverage diagonal cutter						
62120522	High leverage diagonal cutter KSSI 18	3.8	2.7	2.2	0.28	180

Last Update (27.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16