
EPIC® H-A 3 MAGD

Innovative metal and plastic housing design

The compact metal housing for rectangular connectors is supplied with a seal and it is suitable for control systems.

Info
Metal lid with sturdy hinge
Protection rating UL50E tested





Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits
Housing in plastic or metal version for safe connections in the smallest possible space

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features
H-A case: Wall base
1 lever
Metal cover
Included: flat gasket

Last Update (28.03.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-A 3 MAGD

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated zinc die-casting, grey Lever: zinc-plated steel Sealing: NBR Metal cover
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

LAPP

EPIC® H-A 3 MAGD

PRODUCT INFORMATION

Article number	Article description	M	Material	Colour	Pieces / PU
H-A housing: panel-mount base with cover (with sealing, for female inserts)					
44429015	EPIC® H-A 3 MAGD	AG	Aluninium die-casting	grey	10

Last Update (28.03.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16