
EPIC® H-B 10 AG-LB

Housing design H-B. The industry standard.

The robust housing for rectangular connectors with a seal and a single lever can be used, for example, in the plastics industry.

Info

Single Lever version for quick locking and simple unlocking with lifting aid
Protection rating UL50E tested



Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

The smallest housing with single and double lever. The right housing is available for every application

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

H-A case: Wall base

Last Update (12.01.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 10 AG-LB

Single lever
Included: flat gasket

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

EPIC® H-B 10 AG-LB

Article number	Article description	M	Pieces / PU
H-B housing: panel-mount base (single lever)			
10032900	H-B 10 AG-LB	AG	10

©2024 Lapp Group - Technical changes reserved