
FLEXIMARK® Collar closed

FLEXIMARK® Collar halogen free are character holders for marking wires before assembly, halogen free and flame-retardant

Info
Mounting before installation, as marking collar is closed



Flame-retardant

Halogen-free

Benefits
Enhanced scratch-protection
Resistant and flexible protection
Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

Product features
Extremely flame-retardant according to
UL 94 V0

Note
Suitable marking collar for LMB labels

Included
Marking collars without labels

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002248 ETIM 5.0 Class-Description: Mounting for labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002248 ETIM 6.0 Class-Description: Mounting for labelling material
Colour delivered:	Transparent
Material:	PVC
Temperature range:	-40 °C to +80 °C

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Collar closed

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Collar closed

Article number	Article designation	Length (mm)	For cable Ø (mm)	Markers / PU	PU
83252693	FLEXIMARK® collar halogenfree 1,4-5/23 TR	23	1.4 - 5.0	500	1
83252694	FLEXIMARK® collar halogen-free 5-11/23 TR	23	5.0 - 11.0	200	1
83252675	FLEXIMARK® collar halogen-free 5-11/30 TR	30	5.0 - 11.0	200	1
FLEXIMARK® Collar closed					
83252670	FLEXIMARK® collar halogen-free 1.4-5/10 TR	10	1.4 - 5.0	1000	1
83252671	FLEXIMARK® collar halogen-free 1.4-5/15 TR	15	1.4 - 5.0	1000	1
83252672	FLEXIMARK® collar halogen-free 1.4-5/30 TR	30	1.4 - 5.0	500	1
83252673	FLEXIMARK® collar halogen-free 5-11/10 TR	10	5.0 - 11.0	500	1
83252674	FLEXIMARK® collar halogen-free 5-11/15 TR	15	5.0 - 11.0	500	1

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16