FLEXIMARK® Wrapping labels TCK

FLEXIMARK® TCK wrapping labels are markers of vinyl with an protective transparent foil for marking cables with a thermal transfer printer





- Solar Energy
- Wind Energy
- Good chemical resistance
- Halogen-free
- UV-resistant
- Waterproof

Benefits

A transparent film is wrapped around the cable and pasted over the printed field so that the printing is protected against abrasion, pollution and solvents
Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)
Due to tight wrapping, space-saving

Application range

For cable marking

Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2
Recommended ribbon: R71 110-360 resin BK (article no. 83259609)

Included

Delivered as a roll of labels

Last Update (24.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Wrapping labels TCK

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material
Adhesive:	Acrylic-based permanent adhesive
Colour delivered:	White or yellow
Material:	Halogen-free polyester Thickness: 0.025 mm
Temperature range:	-40 °C to +125 °C Minimum working temperature: +10 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

©2024 Lapp Group - Technical changes reserved

LAPP

PRODUCT INFORMATION

FLEXIMARK® Wrapping labels TCK

Article number	Article designation	Colour	Width x length (mm)	Printable surface (W x H mm)	For Ø (mm)	Markers / PU	PU
White version							
83259874	FLEXIMARK® Label TCK 32 WH	white	25.0 x 33.5	25.0 x 12.7	4.0 - 7.0	1200	1
83259875	FLEXIMARK® Label TCK 35 WH	white	25.0 x 55.0	25.0 x 19.0	6.0 - 12.0	1200	1
83259876	FLEXIMARK® Label TCK 40 WH	white	25.0 x 94.0	25.0 x 25.0	8.0 - 21.0	600	1
83259877	FLEXIMARK® Label TCK 45 WH	white	25.0 x 142.5	25.0 x 25.0	8.0 - 36.0	600	1
83259890	FLEXIMARK® Label TCK 48 WH	white	34.0 x 93.0	34.0 x 25.4	8.0 - 21.0	600	1
83259878	FLEXIMARK® Label TCK 60 WH	white	50.0 x 56.0	50.0 x 19.0	6.0 - 12.0	600	1
83259879	FLEXIMARK® Label TCK 65 WH	white	50.0 x 94.0	50.0 x 25.4	8.0 - 21.0	600	1
83259881	FLEXIMARK® Label TCK 70 WH	white	50.0 x 142.5	50.0 x 25.4	8.0 - 36.0	600	1
Yellow version							
83259882	FLEXIMARK® Label TCK 32 YE	yellow	25.0 x 33.5	25.0 x 12.7	4.0 - 7.0	1200	1
83259883	FLEXIMARK® Label TCK 35 YE	yellow	25.0 x 55.0	25.0 x 19.0	6.0 - 12.0	1200	1
83259884	FLEXIMARK® Label TCK 40 YE	yellow	25.0 x 94.0	25.0 x 25.0	8.0 - 21.0	600	1
83259885	FLEXIMARK® Label TCK 45 YE	yellow	25.0 x 142.5	25.0 x 25.0	8.0 - 36.0	600	1
83259889	FLEXIMARK® Label TCK 48 YE	yellow	34.0 x 93.0	34.0 x 25.4	8.0 - 21.0	600	1
83259886	FLEXIMARK® Label TCK 60 YE	yellow	50.0 x 56.0	50.0 x 19.0	6.0 - 12.0	600	1
83259887	FLEXIMARK® Label TCK 65 YE	yellow	50.0 x 94.0	50.0 x 25.4	8.0 - 21.0	600	1
83259888	FLEXIMARK® Label TCK 70 YE	yellow	50.0 x 142.5	50.0 x 25.4	8.0 - 36.0	600	1

Last Update (24.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16