# SILVYN® HG-M

SILVYN® HG-M - conduit fitting for SILVYN® HCC



UV-resistant

## Benefits
Easy to disassemble
High-tensile
Sealing

## Application range
In combination with protective conduit
SILVYN® HCC

## Product Make-up
Metric connection thread
Body with sealing and clamping ring
Cap nut

## Note
UV-resistant and weather-resistant

## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001176<br>ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001176<br>ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose |
| Colour delivered: | Black (RAL 9005), UV-resistant |
| Material: | PA6 |
| Protection rating: | IP 65 |
| Temperature range: | -25 °C to +100 °C |

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# SILVYN® HG-M

**Note**
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# SILVYN® HG-M

| Article number | Article designation | Overall length mm | Thread length mm | Suitable for SILVYN® HCC | Pieces / PU |
|---|---|---|---|---|---|
| 55501650 | 40 x 1,5 | 53 | 15 | 40 | 20 |
| 55501660 | 50 x 1,5 | 57.4 | 15 | 50 | 16 |
| 55501670 | 63 x 1,5 | 74 | 20 | 63 | 8 |

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16