
SILVYN® BRAID PA6

SILVYN® BRAID PA6 is a braided sleeving to protect cables from abrasion

Info
Simple, fast cable bundling





Wide clamping range

Low weight

Reliability

Temperature-resistant

UV-resistant

Benefits
Can be cut without the need for a thermo-cutting tool
Cut into length without frazzle on the conduit's end
Abrasion protection
Simple, fast cable bundling
Protection against dust

Application range
Easy cable protection
Additional insulation
Bundling and guiding of cables and wires
Low rodent-protection

Product features
Abrasion-resistant
Flexible
Can be cut at cold temperatures

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SILVYN® BRAID PA6

Product Make-up
Polyamide 6.6 - halogen-free

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001182 ETIM 5.0 Class-Description: Braided hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001182 ETIM 6.0 Class-Description: Braided hose
On request:	Bulk containers on rolls More sizes available
Note:	Halogen and cadmium-free Fire behaviour according to UL94 V-2
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	Polyamide 6.6 - halogen-free
Temperature range:	-55°C to +125°C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

SILVYN® BRAID PA6

Article number	Nominal size	Clamping range in mm	Colour	PU (m)
SILVYN® BRAID PA6				
61721260	6	4 - 10	black	20
61721261	12	10 - 14	black	15
61721262	16	14 - 24	black	15
61721263	20	18 - 26	black	10
61721264	30	26 - 34	black	10
61721265	40	32.0 - 42.0	black	5

©2024 Lapp Group - Technical changes reserved