KNIPEX High leverage combination plier

KNIPEX Insulated pliers for gripping and cutting work

Info
35 % less effort required than with conventional combination pliers



Benefits
High ergonomics thanks to multi-component handles
Insulated handels allow working under voltage up to 1000V

Application range
With gripping zones for versatile use
With cutting edges for heavy duty and thicker cables

Product features
Long cutting edges for thicker cables

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000836 ETIM 5.0 Class-Description: Combination pliers
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000836 ETIM 6.0 Class-Description: Combination pliers
Certifications:	Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC VDE-tested
Material:	High-grade special tool steel, forged, multi stage oil-hardened

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

KNIPEX High leverage combination plier

Article number	Article designation	Hard wire mm	Pianowire mm	Cable diameter mm	Weight (kg)	Length (mm)
62120504	High leverage combination plier KKZI 20	2.8	2.2	13	0.343	200

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16