SILVYN® LTP-C

SILVYN® LTP coupler - nickel-plated brass conduit coupler

Info
Connection of two conduits



Assembly time

Space requirement

Robust

Reliability

Benefits
Optional extension of SILVYN® LTP
Fast assembly
High tensile strength

Application range
In combination with protective conduit:
SILVYN® LTP
Conduit coupler for extension

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective

©2023 Lapp Group - Technical changes reserved

SILVYN® LTP-C

	metallic hose
Certifications:	IEC EN 61386-23
Material:	Nickel-plated brass
Protection rating:	IP66 IP67 IP68 (5 bar) IP69
Temperature range:	-50 °C to +135 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

SILVYN® LTP-C

Article number	Nominal size	Suitable for SILVYN® LTP	Pieces / PU
SILVYN® LTP-C			
55510310	16	16	2
55510311	20	20	2
55510312	25	25	2
55510313	32	32	2

©2023 Lapp Group - Technical changes reserved