SILVYN® SPLIT GMP-M

SILVYN® SPLIT GMP-M is a divisible counter nut for subsequent installation with the divisible conduit SILVYN® SPLIT

Halogen-free

Assembly time

Temperature-resistant

UV-resistant

Benefits

Fast assembly
Easy to disassemble

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	Halogen-free PA
Temperature range:	-40 °C to +120 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

LAPP

SILVYN® SPLIT GMP-M

PRODUCT INFORMATION

Article number	Metric size	Pieces / PU
SILVYN® SPLIT GMP-M (metric counter nut)		
61806686	16 x 1.5	100
61806688	25 x 1.5	50
61806689	32 x 1.5	50
61806691	40 x 1.5	25
61806687	20 x 1.5	100
61806692	50 x 1.5	25

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16