

EPIC® Protective cover H-B

The protective cover made of thermoplastic is suitable for use with H-B 6, H-B 10, H-B 16, H-BA 24 and H-B 32 housings.



Mechanical resistance



Reliability



Waterproof

Product features

Retaining cord with cable lug for attachment with screw on mounting base or wall

Retaining cord with variable loop for attachment to the cable

Protective cover made of thermoplastics for H-B 6, H-B 10, H-B 16, H-B 24, H-B 32 housings

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002314

ETIM 5.0 Class-Description: Cap for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002314

ETIM 6.0 Class-Description: Cap for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® Protective cover H-B

Article number	Article description	Version	Bolts	Securing cord	Clamp	Material	Pieces / PU
with bolts for H-B 6-24 panel-mount base, surface-mount base, cable coupler hood							
10015000	H-B 6 KDB	for housing H-B 6	2	with loop	-	Plastic	10
10047000	H-B 10 KDB	for housing H-B 10	4	with loop	-	Plastic	10
10087000	H-B 16 KDB	for housing H-B 16	4	with loop	-	Plastic	5
10118000	H-B 24 KDB	for housing H-B 24	4	with loop	-	Plastic	5
with lever for H-B 6-24 hood with bolts							
10016500	H-B 6 KDT	for H-B 6 hood	-	with loop	Single lever	Plastic	10
10048500	H-B 10 KDT	for H-B 10 hood	-	with loop	Double Lever	Plastic	10
10088500	H-B 16 KDT	for H-B 16 hood	-	with loop	Double Lever	Plastic	5
10119500	H-B 24 KDT	for H-B 24 hood	-	with loop	Double Lever	Plastic	5
with bolts for H-B 6-24 hoods with levers							
10015100	H-B 6 KDBP	for H-B 6 hood	2	with loop	-	Plastic	10
10047100	H-B 10 KDBP	for H-B 10 hood	4	with loop	-	Plastic	10
10087100	H-B 16 KDBP	for H-B 16 hood	4	with loop	-	Plastic	10
10118100	H-B 24 KDBP	for H-B 24 hood	4	with loop	-	Plastic	5
with bolts for H-B 10-32 panel-mount base, surface-mount base, cable coupler hood							
10048700	H-B 10 KDBF	for housing H-B 10	2	with loop	-	Plastic	10
10088700	H-B 16 KDBF	for housing H-B 16	2	with loop	-	Plastic	10
10118700	H-B 24 KDBF	for housing H-B 24	2	with loop	-	Plastic	10
10118020	H-B 32 / H-A 48 KDBF	for housing H-B 32/H-A 48	4	with loop	-	Plastic	10
with lever for H-B 10-24 hood with bolts							
10048600	H-B 10 KDTF	for H-B 10 hood	-	with loop	Single lever	Plastic	10
10088600	H-B 16 KDTF	for H-B 16 hood	-	with loop	Single lever	Plastic	10
10118600	H-B 24 KDTF	for H-B 24 hood	-	with loop	Single lever	Plastic	10

EPIC® Protective cover H-B