


FLEXIMARK® Character holders PTE

FLEXIMARK® Character holders PTE for marking cables with labels or character strips. For assembly with cable ties.



Suitable for outdoor use



Good chemical resistance



Halogen-free



Acid-resistant



UV-resistant

Benefits

Additional protection against UV- radiation and diverse chemicals

Ensure high flexibility: Character holders can be cut to the desired length

Application range

Suitable for FLEXIMARK® Flexilabels LFL as well as for DYMO® industry tapes

For cable/conduit marking

Assembly with 2.6 mm cable ties or fasten with screws and rivets when using end caps

Included

Delivery in a plastic bag or in a box (see picture): Character holders in plastic bag are already pre-cut to a particular size

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002248

ETIM 5.0 Class-Description: Mounting for labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002248

ETIM 6.0 Class-Description: Mounting for labelling material

Material:

Halogen-free polyethylene

Temperature range:

-75 °C up to +80 °C

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Character holders PTE

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Character holders PTE

Article number	Article designation	Length (mm)	Max. height of holder (mm)	Markers / PU	PU
83259950	FLEXIMARK® PTE 6-10 m TR (Box)	10000	6	1	1
83252081	FLEXIMARK® PTE 9,5-285 mm TR (Plastic bag)	285	9.5	10	1
83252084	FLEXIMARK® PTE 9,5-1000 mm TR (Plastic bag)	1000	9.5	10	1
83259961	FLEXIMARK® PTE 9.5-15 m TR (Box)	15000	9.5	1	1
83259951	FLEXIMARK® PTE 9.5-10 m TR (Box)	10000	9.5	1	1
83252028	FLEXIMARK® PTE 12-285 mm TR (Plastic bag)	285	12	10	1
83252027	FLEXIMARK® PTE 12-1000 mm TR (Plastic bag)	1000	12	10	1
83259952	FLEXIMARK® PTE 12-10 m TR (Box)	10000	12	1	1
83251060	FLEXIMARK® PTE 19-285 mm TR (Plastic bag)	285	19	10	1
83259953	FLEXIMARK® PTE 19-5 m TR (Box)	5000	19	1	1
83251061	FLEXIMARK® PTE 19-1000 mm TR (Plastic bag)	1000	19	10	1
83259954	FLEXIMARK® PTE 25-5 m TR (Box)	5000	25	1	1
Accessories for character holder PTE 9.5mm					
83252005	FLEXIMARK® Lock Button Mini FLKA 5206 YE	-	-	500	1
83252020	FLEXIMARK® End clap Mini FLG 5242 YE	-	-	100	1