

## FLEXIMARK® LA Labels

FLEXIMARK® LA Labels are self-adhesive markers for component marking in the electrical industry (e.g. marking cabinets).

### Info

LA 16.9-9 YE included in FLEXIMARK® sample bag (article no. M3251010)



Halogen-free



UV-resistant

### Benefits

Self-adhesive labels made from polyester film for laser printers

Better grip due to rounded-corners

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

### Application range

For component marking e.g. for marking cabinets

### Product features

Adhesive needs up to 24 hours to bond

### Note

Can be printed with the FLEXIMARK® Software and a commercial laser printer

Insert sheet in manual paper feed compartment

Optimum printing results from laser printers are achieved with straight sheet feed-in

### Included

Perforated DIN A4 sheets

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001288

ETIM 6.0 Class-Description: Labelling material

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® LA Labels

|                    |                                                        |
|--------------------|--------------------------------------------------------|
| Adhesive:          | Acrylic-based permanent adhesive                       |
| Colour delivered:  | White or yellow<br>Also available in silver            |
| Material:          | Halogen-free polyester<br>Thickness: 0.05 mm           |
| Temperature range: | -40 °C to +150 °C<br>Mounting temperature: min. +10 °C |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

# FLEXIMARK® LA Labels

| Article number | Article designation                 | Colour | Width x height (mm) | Labels per side | Markers / PU | PU |
|----------------|-------------------------------------|--------|---------------------|-----------------|--------------|----|
| 83256199       | FLEXIMARK® LA label<br>7-8 YE       | yellow | 7.0 x 8.0           | 560             | 5600         | 1  |
| 83256228       | FLEXIMARK® LA label<br>11-8 YE      | yellow | 11.0 x 8.0          | 420             | 4200         | 1  |
| 83256231       | FLEXIMARK® LA label<br>12-6 YE      | yellow | 12.0 x 6.0          | 611             | 6110         | 1  |
| 83256204       | FLEXIMARK® LA label<br>15-6 YE      | yellow | 15.0 x 6.0          | 517             | 5170         | 1  |
| 83256234       | FLEXIMARK® LA label<br>16-8 YE      | yellow | 16.0 x 8.0          | 315             | 3150         | 1  |
| 83256207       | FLEXIMARK® LA label<br>16.9-7 YE    | yellow | 16.9 x 7.0          | 400             | 4000         | 1  |
| 83256210       | FLEXIMARK® LA label<br>16.9-9 YE    | yellow | 16.9 x 9.0          | 310             | 3100         | 1  |
| 83256213       | FLEXIMARK® LA label<br>20-8 YE      | yellow | 20.0 x 8.0          | 280             | 2800         | 1  |
| 83256216       | FLEXIMARK® LA label<br>25-12 YE     | yellow | 25.0 x 12.0         | 161             | 1610         | 1  |
| 83256219       | FLEXIMARK® LA label<br>25.6-10 YE   | yellow | 25.6 x 10.0         | 196             | 1960         | 1  |
| 83256240       | FLEXIMARK® LA label<br>30.5-12.7 YE | yellow | 30.5 x 12.7         | 110             | 1100         | 1  |
| 83256222       | FLEXIMARK® LA label<br>46.9-9 YE    | yellow | 46.9 x 9.0          | 124             | 1240         | 1  |
| 83256225       | FLEXIMARK® LA label<br>56-21.8 YE   | yellow | 56.0 x 21.8         | 39              | 390          | 1  |
| 83256243       | FLEXIMARK® LA label<br>60-30 YE     | yellow | 60.0 x 30.0         | 27              | 270          | 1  |
| 83256237       | FLEXIMARK® LA label<br>80-7.5 YE    | yellow | 80.0 x 7.5          | 74              | 740          | 1  |
| 83256198       | FLEXIMARK® LA label<br>7-8 WH       | white  | 7.0 x 8.0           | 560             | 5600         | 1  |
| 83256230       | FLEXIMARK® LA label<br>12-6 WH      | white  | 12.0 x 6.0          | 611             | 6110         | 1  |
| 83256203       | FLEXIMARK® LA label<br>15-6 WH      | white  | 15.0 x 6.0          | 517             | 5170         | 1  |
| 83256233       | FLEXIMARK® LA label<br>16-8 WH      | white  | 16.0 x 8.0          | 315             | 3150         | 1  |
| 83256206       | FLEXIMARK® LA label<br>16.9-7 WH    | white  | 16.9 x 7.0          | 400             | 4000         | 1  |
| 83256209       | FLEXIMARK® LA label                 | white  | 16.9 x 9.0          | 310             | 3100         | 1  |

# FLEXIMARK® LA Labels

| Article number | Article designation                 | Colour | Width x height (mm) | Labels per side | Markers / PU | PU |
|----------------|-------------------------------------|--------|---------------------|-----------------|--------------|----|
|                | 16.9-9 WH                           |        |                     |                 |              |    |
| 83256212       | FLEXIMARK® LA label<br>20-8 WH      | white  | 20.0 x 8.0          | 280             | 2800         | 1  |
| 83256215       | FLEXIMARK® LA label<br>25-12 WH     | white  | 25.0 x 12.0         | 161             | 1610         | 1  |
| 83256218       | FLEXIMARK® LA label<br>25.6-10 WH   | white  | 25.6 x 10.0         | 196             | 1960         | 1  |
| 83256239       | FLEXIMARK® LA label<br>30.5-12.7 WH | white  | 30.5 x 12.7         | 110             | 1100         | 1  |
| 83256221       | FLEXIMARK® LA label<br>46.9-9 WH    | white  | 46.9 x 9.0          | 124             | 1240         | 1  |
| 83256224       | FLEXIMARK® LA label<br>56-21.8 WH   | white  | 56.0 x 21.8         | 39              | 390          | 1  |
| 83256242       | FLEXIMARK® LA label<br>60-30 WH     | white  | 60.0 x 30.0         | 27              | 270          | 1  |
| 83256236       | FLEXIMARK® LA label<br>80-7.5 WH    | white  | 80.0 x 7.5          | 74              | 740          | 1  |
| 83256200       | FLEXIMARK® LA label<br>7-8 SR       | silver | 7.0 x 8.0           | 560             | 5600         | 1  |
| 83256229       | FLEXIMARK® LA label<br>11-8 SR      | silver | 11.0 x 8.0          | 385             | 3850         | 1  |
| 83256232       | FLEXIMARK® LA label<br>12-6 SR      | silver | 12.0 x 6.0          | 611             | 6110         | 1  |
| 83256235       | FLEXIMARK® LA label<br>16-8 SR      | silver | 16.0 x 8.0          | 315             | 3150         | 1  |
| 83256241       | FLEXIMARK® LA label<br>30.5-12.7 SR | silver | 30.5 x 12.7         | 110             | 1100         | 1  |
| 83256244       | FLEXIMARK® LA label<br>60-30 SR     | silver | 60.0 x 30.0         | 27              | 270          | 1  |
| 83256238       | FLEXIMARK® LA label<br>80-7.5 SR    | silver | 80.0 x 7.5          | 74              | 740          | 1  |
| 83256096       | -                                   | -      | -                   | -               | -            | -  |
| 83256097       | -                                   | -      | -                   | -               | -            | -  |