

## TRONIC Single core cart

Mobile and flexible solutions to unwind, store and transport single core coils and spools.

### Info

TRONIC products are optimized for LAPP single core coils H05V-K and H07V-K (Maxi ring) as well as for LAPP single core spools.



### Benefits

- Easy and mobile handling and storage of single core coils and spools and increases occupational safety and tidy workplaces
- Direct bundling of single cores at the operation site leads to efficient assembly
- User-friendly solution because of short setup times due to an easy refill
- No twisting / kinking through horizontal pull
- Mounting of barcodes enables to use kanban solutions, furthermore FLEXIMARK® markings are also possible

### Application range

- Transporting, storing and unwinding of single core coils and spools
- Overcoming stairs and other barriers with the Climber version
- All in one compact mobile storage and unwinding solution for the operational site

### Product features

- TRONIC module consists of 2 TRONIC boxes mounted on a holder
- TRONIC Single core-cart S12:
- Capacity for 12 to 18 single core spools (depending on spools width)
- Cart with tool holder
- TRONIC Module single core cart Climber with stair climber and optionally a tray for tools (article no.: 85001640)

### Technical Data

Dimensions:

Fits for cable rings:  
Cable outer diameter: max. 10 mm  
Coil Diameter: max. 295 mm  
Inner diameter: 80-180 mm  
Height: max. 80 mm

General data:

Max. load per TRONIC: 7 kg  
Max. loading TRONIC Single core-cart S12:  
1. Level: 60 kg  
2. Level: 40 kg  
3. Level: 30 kg

Material:

Painted steel

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## TRONIC Single core cart

**Note**

TRONIC is a brand name of the company Meccanica Nicoletti S.R.L.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

## TRONIC Single core cart

Article number	Article designation	Includes	Capacity of rings	Dimension in mm	Weight (kg)
Box					
85001632	TRONIC Box	-	1	D=310.0, H=103.0	0.7
85001624	TRONIC Single core cart 12	12 TRONIC	12	L=670.0, W=610.0, H=950.0	19
85001629	TRONIC Single core cart 48	48 TRONIC	48	L=865.0, W=770.0, H=1460.0	106
Modul					
85001625	TRONIC Module	2 TRONIC	2	L=335.0, W=335.0, H=280.0	2.6
85001621	TRONIC Module single core cart 6x2	6 TRONIC Module	12	L=610.0, W=600.0, H=1270.0	29
85001622	TRONIC Module single core cart 18x2	18 TRONIC Module	36	L=840.0, W=820.0, H=1400.0	93
85001639	TRONIC Module single core cart Climber	6 TRONIC Module	12	L=710.0, W=680.0, H=1360.0	40
Accessories					
85001637	TRONIC cover	1 transparentní víko	-	-	-

## TRONIC Single core cart

