
# EPIC® H-A 3 AGS

Innovative metal and plastic housing design

The robust angular housing for placement in rectangular connectors can be used, for example, in electronic laboratories.

## Info
Lightweight, chemically resistant plastic housing
Protection rating UL50E tested





Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

## Benefits
Housing in plastic or metal version for safe connections in the smallest possible space

## Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

## Product features
H-A case: Wall base
1 lever
Angled version
Included: flat gasket

Last Update (29.03.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# EPIC® H-A 3 AGS

## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437<br>ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437<br>ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | Housing: powder-coated zinc die-casting, grey<br>Lever: zinc-plated steel<br>Sealing: NBR<br>Housing: grey thermoplastic, black<br>Lever: zinc-plated steel<br>Sealing: NBR |
| Protection rating: | IP 65 (latched)<br>NEMA 250, UL50E: 12, 4 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437<br>UL-tested:<br>UL File Number: E75770 |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |

## Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.


©2024 Lapp Group - Technical changes reserved

LAPP

# EPIC® H-A 3 AGS


PRODUCT INFORMATION

| Article number | Article description | M | Material | Colour | Pieces / PU |
|---|---|---|---|---|---|
| H-A housing: panel-mount base (angled) | | | | | |
| 10423500 | H-A 3 Mags | AG | Zinc die-casting | grey | 10 |
| 10423100 | H-A 3 Ags | AG | Thermoplastic | black | 10 |
| 10423000 | H-A 3 Ags | AG | Thermoplastic | grey | 10 |

Last Update (29.03.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# EPIC® H-A 3 AGS







©2024 Lapp Group - Technical changes reserved