


EPIC® QUICK & EASY Mounting system

The installation system for control cabinets is available as a set or as single components (upper part for the cable connector, lower part for installation to DIN rail).

Info

Mounting system for control cabinets



Application range

Control cabinet manufacturing

Product features

For mounting inserts on top-hat rails according to DIN EN 50022

Available as a complete set or as single parts (top part for use as a cable connector, bottom part for mounting on a top-hat rail)

QUICK & EASY top parts are available in housing types H-B 6, H-B 10, H-B 16, H-B 24. The suitable size (number of contacts) of the different insert types are listed at the connector housings (H-B 6 ..H-B 24)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002312

ETIM 5.0 Class-Description: Contact insert holder for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002312

ETIM 6.0 Class-Description: Contact insert holder for industrial connectors

Flammability:

UL94 V-0

Cycle of mechanical operation:

50

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® QUICK & EASY Mounting system

| Article number | Article description | Material | Version | Pieces / PU |
|---------------------------|--------------------------------|---------------|-----------------------------------|-------------|
| QUICK & EASY complete set | | | | |
| 10027000 | EPIC® H-B 6 Q+E Set | Polycarbonate | Complete, for inserts size H-B 6 | 1 |
| 10027100 | EPIC® H-B 10 Q+E Set | Polycarbonate | Complete, for inserts size H-B 10 | 1 |
| 10027200 | EPIC® H-B 16 Q+E Set | Polycarbonate | Complete, for inserts size H-B 16 | 1 |
| 10027300 | EPIC® H-B 24 Q+E Set | Polycarbonate | Complete, for inserts size H-B 24 | 1 |
| QUICK & EASY top part | | | | |
| 10027410 | EPIC® H-B 6 Q+E top part | Polycarbonate | For inserts size H-B 6 | 10 |
| 10027510 | EPIC® H-B 10 Q+E top part | Polycarbonate | For inserts size H-B 10 | 10 |
| 10027610 | EPIC® H-B 16 Q+E top part | Polycarbonate | For inserts size H-B 16 | 10 |
| 10027710 | EPIC® H-B 24 Q+E top part | Polycarbonate | For inserts size H-B 24 | 10 |
| QUICK & EASY bottom part | | | | |
| 10027810 | EPIC® H-B 6-24 Q+E bottom part | Polycarbonate | For inserts size H-B 6 - 24 | 10 |