FLEXIMARK® Collar Snap-on

FLEXIMARK® collars for marking single cores before or after assembly.

Info

Mounting after installtion possible by snap-on mechanism
Snap-On 2-3,5/15 included in FLEXIMARK® sample bag (article no. M3251010)





Flame-retardant

Halogen-free

Benefits

Enhanced scratch-protection
Resistant and flexible protection
Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

Product features

Extremely flame-retardant according to
UL 94 V0

Note

Suitable marking collar for LMB labels

Included

Marking collars without labels

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002248 ETIM 5.0 Class-Description: Mounting for labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002248 ETIM 6.0 Class-Description: Mounting for labelling material
Colour delivered:	Transparent
Material:	Halogen-free polyethylene
Temperature range:	-40 °C to +80 °C

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Collar Snap-on

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

LAPP

FLEXIMARK® Collar Snap-on

PRODUCT INFORMATION

Article number	Article designation	Length (mm)	For cable Ø (mm)	Markers / PU	PU
FLEXIMARK® Collar Snap-on					
83252650	FLEXIMARK® collar SnapOn 2-3.5/10 TR	10	2 - 3.5	1000	1
83252651	FLEXIMARK® collar SnapOn 2-3.5/15 TR	15	2 - 3.5	1000	1
83252695	FLEXIMARK® collar SnapOn 2-3.5/23 TR	23	2 - 3.5	500	1
83252653	FLEXIMARK® collar SnapOn 2.8-5/10 TR	10	2.8 - 5	1000	1
83252654	FLEXIMARK® collar SnapOn 2.8-5/15 TR	15	2.5 - 5	1000	1
83252656	FLEXIMARK® collar SnapOn 5-8/10 TR	10	5 - 8	500	1
83252657	FLEXIMARK® collar SnapOn 5-8/15 TR	15	5 - 8	500	1
83252660	FLEXIMARK® collar SnapOn 8-10/15 TR	15	8 - 10	500	1

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16