


## FLEXIMARK® Collar closed

FLEXIMARK® Collar halogen free are character holders for marking wires before assembly, halogen free and flame-retardant

### Info

Mounting before installation, as marking collar is closed



Flame-retardant



Halogen-free

### Benefits

Enhanced scratch-protection

Resistant and flexible protection

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)

### Product features

Extremely flame-retardant according to  
UL 94 V0

### Note

Suitable marking collar for LMB labels

### Included

Marking collars without labels

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002248

ETIM 5.0 Class-Description: Mounting for labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002248

ETIM 6.0 Class-Description: Mounting for labelling material

Colour delivered:

Transparent

Material:

PVC

Temperature range:

-40°C to +80°C

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## **FLEXIMARK® Collar closed**

### **Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

**FLEXIMARK® Collar closed**

Article number	Article designation	Length (mm)	For cable Ø (mm)	Markers / PU	PU
83252693	FLEXIMARK® collar halogenfree 1,4-5/23 TR	23	1.4 - 5.0	500	1
83252694	FLEXIMARK® collar halogen-free 5-11/23 TR	23	5.0 - 11.0	200	1
83252675	FLEXIMARK® collar halogen-free 5-11/30 TR	30	5.0 - 11.0	200	1
FLEXIMARK® Collar closed					
83252670	FLEXIMARK® collar halogen-free 1.4-5/10 TR	10	1.4 - 5.0	1000	1
83252671	FLEXIMARK® collar halogen-free 1.4-5/15 TR	15	1.4 - 5.0	1000	1
83252672	FLEXIMARK® collar halogen-free 1.4-5/30 TR	30	1.4 - 5.0	500	1
83252673	FLEXIMARK® collar halogen-free 5-11/10 TR	10	5.0 - 11.0	500	1
83252674	FLEXIMARK® collar halogen-free 5-11/15 TR	15	5.0 - 11.0	500	1

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16