

# FLEXIMARK® Flexiprint FCC

FLEXIMARK® FLEXIPRINT FCC are markers with customized text for threading on single cores and fibre optic cables, quick and easy to install.




- Good chemical resistance
- Halogen-free
- Assembly time
- UV-resistant

## Benefits

Customised printed labels in various sizes
Easy to install
Good UV resistance

## Application range

For single core marking
Marking before assembly
Marking of optical fibre cables

## Note

Markers will be delivered with the desired text (printing service is included in the price)
Normal version: Up to 7 characters
L version (e.g. LF1L): Up to 15 characters
Ordering process: Customer-specific data will be emailed as an Excel file to the responsible Lapp employee when the order is made
Column A: Row 1 content
Column B: Row 2 content
Column B or C: Number of markers with corresponding text
Print jobs template: www.lappkabel.com/service/downloadcenter/markingsystem/fleximark-customized-markings.html

## Included

1 PU= 1 marker, there is no mimimum purchase quantity

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# FLEXIMARK® Flexiprint FCC

## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001288<br>ETIM 5.0 Class-Description: Labelling material |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001288<br>ETIM 6.0 Class-Description: Labelling material |
| Colour delivered: | White<br>Also available in yellow, green, blue and red |
| Material: | Halogen-free polyester<br>Thickness: 0.175 mm |
| Temperature range: | -40 °C to +125 °C |

## Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.


©2024 Lapp Group - Technical changes reserved

LAPP

# FLEXIMARK® Flexiprint FCC

PRODUCT INFORMATION

| Article number | Article designation | Colour | A (mm) | B (mm) | C (mm) | D (mm) | E (mm) | For mm² | Markers / PU |
|---|---|---|---|---|---|---|---|---|---|
| 83251101 | FLEXIMARK® Flexiprint F0 WH FCC | white | 22.9 | 5.2 | 3.9 | 13.1 | 2.4 | 0.25 - 0.75 | 1 |
| 83251111 | FLEXIMARK® Flexiprint F1 WH FCC | white | 23 | 5.2 | 4.9 | 11.2 | 3.5 | 0.75 - 1.5 | 1 |
| 83251121 | FLEXIMARK® Flexiprint F1B WH FCC | white | 25 | 5.7 | 5.9 | 11.2 | 4.2 | 1.5 - 2.5 | 1 |
| 83251131 | FLEXIMARK® Flexiprint F2 WH FCC | white | 26 | 7 | 6.5 | 11 | 5.5 | 2.5 - 6.0 | 1 |
| 83251141 | FLEXIMARK® Flexiprint F3 WH FCC | white | 41 | 11 | 10.5 | 17 | 8.4 | 6.0 - 16.0 | 1 |

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16